# **FX-iWP Series Washdown**

## **Standard Features**

- Washdown IP65 rating
- Compact Super Hybrid Sensor Technology (SHS)
- Vacuum Fluorescent Display (VFD)
- GLP/GMP/ISO compliant to either AD-8121 printer or computer. Transmits date, time, ID number, serial number and calibration data.
- · RS-232 interface for connecting to printer or PC
- · Response indicator function
- Underhook weighing

# **Specifications**

### Weighing Units:

Carat, pennyweight, troy ounce, grain, pound/ounce (see technical manual for complete listings)

#### **Operating Modes:**

Weigh, count, percent, animal weighing, statistical, hold and comparator

#### Power:

120/240 VAC adapter, approx. 11 VA

#### Stabilization Time:

Approx. 1 second

#### Display Refresh Rate:

5 times/second, 10 times/second or 20 times/second

# **Calibration Weight:**

FX-120iWP: 100 g FX-200iWP: 200 g FX-300iWP: 300 g

#### Temperature:

Operating:

41 °F to 104 °F (5 °C to 40 °C)

#### **Humidity:**

85% RH or less (no condensation)

#### Est. Weight:

8 lb (3.5 kg)

#### Warranty:

Five-year limited

#### Return Policy:

A&D Weighing standard policy restock fee may apply

Model	Capacity	Readability	Repeatability	Linearity	Pan Size	Dimensions	Part #	List Price
FX-120iWP	122 g	0.001 g	0.001 g	±0.002 g	Ø 5.12 in (130 mm)	6 × 10.3 × 3.3 in (193 × 263 × 85 mm)	102905	Consult
FX-200iWP	220 g	0.001 g	0.001 g	±0.002 g	Ø 5.12 in (130 mm)	6 × 10.3 × 3.3 in (193 × 263 × 85 mm)	102906	Consult
FX-300iWP	320 g	0.001 g	0.001 g	±0.002 g	Ø 5.12 in (130 mm)	6 × 10.3 × 3.3 in (193 × 263 × 85 mm)	102907	Consult

# **Options/Accessories**

Part#	A&D Model#	Description	Price
98027*	FXi-02	Quick USB interface	Consult
98028*	FXi-08	Ethernet interface with WinCT© Plus software	Consult
98029*	FXi-09	Built-in rechargeable battery	Consult
98030	FXi-10	Small breeze break	Consult
98031	FXi-11	Large breeze break	Consult
97649	TB:648	AC adapter (120 V/220 V)	Consult

<sup>\*</sup>Options FXi-02/FXi-08 and FXi-09 cannot be combined and are factory installed only.

