

6. Place weight equal to full scale capacity on the platter. Press **UNITS** key.


For an instant, "CAL" is displayed and the counts will be set "35000."

(ZERO = 5000) + (FULL CAPACITY = 30000 counts) = 35000 counts




- Remove the weight from the platter before tipping over the scale cover.

7. Please press the memory switch located next to the AC/DC adaptor connector to keep this setting. Display will only show this momentarily.



- The precision adjustment switch is located on the bottom of the balance, near the screw for the right front foot.
- Press it into the hole with a long, blunt object (e.g. the tip of a pen).



8. Press **ON/OFF** key for a few seconds to power off.

6. Specifications

Platter Size	9.1" × 7.8"	11.0" × 11.5"
Capacity and minimum graduation	3 kg/6 lb	15 kg/30 lb
	1.5 kg × 0.001 kg	7.5 kg × 0.005 kg
	3 kg × 0.002 kg	15 kg × 0.01 kg
	3 lb × 0.002 lb	15 lb × 0.01 lb
	6 lb × 0.005 lb	30 lb × 0.02 lb
	6 kg/15 lb	30 kg/60 lb
	3 kg × 0.002 kg	15 kg × 0.01 kg
	6 kg × 0.005 kg	30 kg × 0.02 kg
	7.5 lb × 0.005 lb	30 lb × 0.02 lb
	15 lb × 0.01 lb	60 lb × 0.02 lb
POWER	Dry Cell 2 pieces (* can be operated for 500 hours with alkaline dry D-Type batteries) or AC Adaptor (No Dry Cell and/or AC adaptor are included in the shipment.)	
APPROVALS	NTEP	

Ishida Co., Ltd
Warranty & Service Policy

Statement of Limited Warranty

Subject to the terms and conditions as stated herein, Ishida Co., Ltd, (hereafter referred as "Ishida") warrants its equipment to be free from defective in material and factory workmanship for a period of twelve months from the date of installation.

Terms and Conditions of Limited Warranty

This obligation is limited exclusively to defective original equipment manufactured or supplied by Ishida and is subject to the inspection and analysis by Ishida as to conclusively identify or confirm the nature and cause of failure.

Ishida responsibility is confined to repair, replacement, or credit (as its option) of equipment or parts and does not extend coverage to labor, material, or service charges involved in removal of equipment for return to the factory.

This warranty is not applicable for expenses either direct or consequential that may arise from the user or inability to use these products.

Ishida reserves the right to incorporate improvements in material and design of the products without notice and is not obligated to incorporate the same improvements in equipment previously manufactured.

In certain cases, such as used equipment or peripheral equipment not manufactured by Ishida, a reduced warranty may apply. Specific details to these exceptions are provided separately or at the time of purchase.

Ishida shall not be obligated under any warranty different from its warranty as set forth herein. Ishida warranty is limited to the initial customer and installation and is not intended to insure to the benefit of a secondary owner in the event of resale.

Condition Which Void Limited Warranty

This warranty shall not Apply to equipment which:

- 1) Has had repairs or modifications not authorized by Ishida which in Ishida judgment has affected the performance or reliability.
- 2) Has been subject to misuse, negligent handling, accident, damage by fire, water, submersion, or act of God.
- 3) Has had serial number altered, defaced or removed.